

Accessories

SD Memory Cards

Memory Cards	NZ1MEM-2GBSD	NZ1MEM-4GBSD	NZ1MEM-8GBSD	NZ1MEM-16GBSD
Stocked Item	S	S	S	-
Type	SD Memory Card	SDHC Memory Card		
Capacity	2GB	4GB	8GB	16GB
Number of Writings (*1)	60000 times	100000 times		
External Dimensions (H x W x D) mm	32 x 24 x 2.1			
Weight (g)	2			

Note 1: The number indicates the number of files and folders (including system files and system folders) can be created in the root directory on the condition that the number of characters in the file or folder name is 13 or less. In a subdirectory, up to 32767 folders can be created.

Extended SRAM Cassette

Item	NZ2MC-1MBS	NZ2MC-2MBS	NZ2MC-4MBS	NZ2MC-8MBS
Stocked Item	S	S	S	S
Capacity	1M bytes	2M bytes	4M bytes	8M bytes
Number of Insertions and Removals	Limited to 50 times			
External Dimensions (H x W x D) mm	49 x 32 x 18.5			
Weight (g)	20			

Batteries

Model Number	Q6BAT	Q7BAT (*1)
Stocked Item	S	S
Type	Manganese dioxide lithium primary battery	
Initial Voltage	3.0V	
Nominal Current	1800mAh	5000mAh
Battery Life When Not Used	Approximately 5 years (room temperature)	
Lithium Content (g)	0.49	1.52
Application	To hold backup data and clock data	

Note 1: The Q7BAT-SET includes a battery holder.

Blank Cover Module

Model Number	RG60
Stocked Item	S
Number of Occupied I/O Points	Default: 16 points (can be changed to 0, 16, 32, 48, 64, 128, 256, 512, or 1024 points in the I/O assignment setting of the system parameters)
Application	Used for dust prevention in space where an I/O module is not mounted (especially the empty slot between modules)
External Dimensions (H x W x D) mm	106 x 27.8 x 110
Weight (kg)	0.07

DIN Rail Adapter

Model Number	R6DIN1
Stocked Item	S
Applicable Base Units	R3_B, R3_B-HT, R6_B, R6_B-HT, R3_RB, R3_RB-HT, R6_RB, R6_RB-HT