

iQ Platform-compatible PAC System Recorder



Total maintenance solution




management to the next level



Mitsubishi Electric's solution for improving productivity through easier data management

Maintenance is critical for ensuring continuous production. Maintenance includes **Opredictive maintenance** to detect signs of error, periodical **Opreventive maintenance**, and **Ocorrective maintenance** for **prompt troubleshooting** at the time of failure. Mitsubishi Electric proposes an enhanced maintenance solution by recording and sampling production and machine operating data and utilizing this data within various stages of maintenance.

The system recorder is a **3** corrective maintenance solution that ensures prompt troubleshooting and error prevention.



System-wide recording	4
Control data	5
Device/label collection every (programmable controller) scan	5
Recording method according to applications	6
Extensive recording trigger settings	6
Automatic saving to file server	7
Record video feeds at the moment an error occurs	
with network cameras	7
Video data	8
Optimized focusing on camera subject	8
Support high resolution and long-duration recording	8
Collecting all servo axis data in real-time	8
Co-recording function enables easier error cause identification by recording entire system data within compatible modules*1	NEW
Error cause identification via network across entire system by co-recording compatible modules*1 NEW	9
Event history	10
Record event history	10
Record operation log and alarm history	10

Simplified analysis	11
Log marker function	
Difference extraction function	
Offline monitoring. GX LogViewer GX Works3 GT Designer3	13
Data flow analysis function	14
Simplified analysis of motion control	14
Simplified analysis using panel computer	

^{*1.} The recorder module, camera recorder module, and motion CPU module are supported. The motion module will be supported in the future.

System recorder

The system recorder is a corrective maintenance solution that ensures effective resumption of operations reducing downtime through its extensive system-wide data recording and simplified analysis software features.

System-wide recording and simplified analysis

System-wide recording

Extensive recording ensures simpler cause analysis

Error cause identification is made simpler by the extensive recording of various equipment and device data together with a real-time video feed reducing the need for multiple retesting due to insufficient data.

System-wide recording

Irregularities between various equipment including control and drive systems together with operations are all linked.

Automatic system-wide recording

Recording of errors that can occur outside standard operating shifts.

Record entire system data HHH() B O

- Programmable controller CPU (entire bit, word data, project data)
 Servo status (command position, actual position, speed, torque)
- Network camera video feedDisplay and operation log of GOT (HMI)

Simplified analysis

Extensive data shown in the same timeline

Waveform, data, program, operations log, and video feeds are shown in sequence ready for analysis.


■ Easier cause identification


Data flow analysis makes understanding the root-cause of failures easier by showing the relationship between failed and normal devices.

Structured program ensures easier troubleshooting

Supports structured programs and device labels enabling easier resolution of problems, thereby reducing TCO*1.

*1. TCO: Total Cost of Ownership





System-wide recording

System-wide total data recording




Without the system recorder

- Difficult to identify the error cause from data after an error event. Need to collect as much data as
 possible for evidence
- Unable to stay to wait for an anomaly that rarely occurs
- When an error occurs, saving video feed is not possible
- One programmable controller CPU data is not enough to solve problems in large and expanding systems

With the system recorder

- Record all device/label per programmable controller scan
- Video feeds can also be recorded with easy and extensive trigger settings
- In addition to devices/labels; motion module/motion CPU module control data, event history from the programmable controller, GOT (HMI) operation history can also be recorded



System-wide recording Control data

Device/label collection every (programmable controller) scan


1 Collecting of all device and label data

- The MELSEC iQ-R Series recorder module and camera recorder module can automatically collect all device and label data per programmable controller scan prior to and after an error event (together with a time-stamp)
- Complete collection of data necessary for analysis ensures simpler error analysis, reducing the recovery time of the control system
- · Safety device and label collection are also supported


@Easy setting

- The recorder module and camera recorder module can be set within the intuitive engineering software GX Works3
- Target device and labels to be recorded are automatically set by checking the box
- Influence on the CPU scan time can be checked

19 Minimal impact on the scan time



- The modules are designed to separate load from the CPU module, minimizing impact to control
- Influence on the CPU scan time is further minimized by filtering of devices and labels
- Collecting targets can be quickly set by narrowing down with filter conditions



Select multiple filter conditions to narrow down specific devices or labels


Recording method according to applications

Recording of data prior to and after an error event

• Two saving period settings are available with the MELSEC iQ-R Series recorder module/camera recorder module. In addition to recording of data prior to and after the event, data can be recorded starting from the beginning of the equipment cycle

Record prior to and after an error event (file saving trigger only)


Record data prior to and after a file saving trigger for a specified time. Setting equipment alarm relay as a file saving trigger enables recording of data prior to and after the error event.



- The total of the saving periods before and after trigger can be set within a range from 1 to 86400 seconds
- When the recording buffer capacity is exceeded, the old data is overwritten

②Record equipment cycle (recording startup trigger + file saving trigger)

Record data after a recording startup trigger for a specified time. Setting starting relay of equipment cycle as a recording startup trigger enables recording from cycle start.



- If recording startup trigger and such are set, data is saved without a file saving trigger
- The previous recording buffer is overwritten per recording startup trigger
- If the data exceeds the recording buffer capacity in a single recording, old data is prioritized and the data exceeding the capacity is discarded

Extensive recording trigger settings

- The recorder module/camera recorder module are available with extensive triggers for recording which can be used according to requirements
- Setting triggers enables non-alarm stop detection and motion detection, errors previously undetectable can now be detected

Non-alarm stop detection At normal operation Error Non-alarm stop


- Active signals are monitored periodically to detect a signal which remains unchanged for a certain period as timeout
- Used to detect a machine that stops without alarm

Trigger occurrence Save Motion detection

- Monitor equipment and operators with network cameras to trigger when motions are detected
- * Motion detection is supported by the camera recorder module only.
- * For details of compatible camera, please refer to the technical bulletin (FA-A-0326).


Automatic saving to file server

- As a recording file storage, an SD memory card for the system recorder modules or a file server (such as a NAS or computer) can be selected
- A file server (such as a NAS or computer) can be used as storage for a large capacity data. Remote retrieval of collected data directly from the file server is supported without requiring access on the shop floor



Record video feeds at the moment an error occurs with network cameras

- By supporting available network cameras, the camera recorder module offers a wide choice of functions, specific to an application and installation environment
- Network cameras (such as image resolution, frame rate) can be set within GX Works3 without requiring individual setup



Modular type: Installable within control enclosures with limited space Wireless type: Greater installation flexibility as communication cables are not required

Installation environment	Applicable cameras
Wide-area coverage capturing entire process area Recording personnel operations	Wide angle/fish-eye lens type
Detailed view Multiple viewing positions	Optical zoom type PTZ (Pan-Tilt-Zoom) type
Limited installation space Difficulty installing communications cabling	Modular type Wireless type


^{*} For details of compatible cameras, please refer to the technical bulletin (FA-A-0326).

System-wide recording

Video data

Optimized focusing on camera subject

- Live image streaming of the network camera on the GOT (HMI) and MELIPC MI3000 and also PTZ (Pan-Tilt-Zoom) control are possible
- Machine movement can be checked from the GOT (HMI) and MELIPC MI3000
- Fine adjustments are supported while monitoring the live video feed on the shop floor



Support high resolution and long-duration recording

- The system recorder stores high-definition video feeds for a long time using the H.264 codec which compresses the data, making space utilization more efficient
- Since it uses a general-purpose video format, there is no need to move or process the storage location of the video file. In addition, recorded video feeds can be checked instantly by a general video replay software as well as dedicated GX VideoViewer and GX VideoViewer Pro


Collecting all servo axis data in real-time

Recording of positional data from servo

- Servo systems tend to operate at a much faster cycle time compared with a programmable controller making it difficult to capture. Control data of the motion CPU module and motion module can be recorded with a time-stamp
- Detailed positional data from the servo can be recorded


2 Automatic collection without requiring a program

- Simple parameter settings enable the data collection without programming
- Speed/torque/positional data of the MELSERVO-J5/MELSERVO-J4 Series servo amplifier connected with the MELSEC iQ-R Series motion module/motion CPU module are automatically collected as logging data when an error occurs
- Data with a time-stamp is saved in the SD memory card of the motion module/motion CPU module




Co-recording function enables easier error cause identification by recording entire system data within compatible modules*1 NEW

- When any of the compatible modules*1 detects an error, all data recorded in the system is saved at the same time
- By comparing the control data for each module and video feeds when an error occurs, the error cause within multiple devices can be easily analyzed



Error cause identification via network across entire system by co-recording compatible modules*1 NEW

- Errors detected by any of compatible modules*1 are notified to other stations via CC-Link IE TSN
- Even in a large-scale production line with multiple equipment/processes, error factors across programmable controllers can be easily analyzed by aligning a specific timeline




^{*1.} The recorder module, camera recorder module, and motion CPU module are supported. The motion module will be supported in the future.

System-wide recording Event history

Record event history


- Operation from engineering software and device/label operation from external devices can be recorded as historical events
- By analyzing event history with records of device/label changes when an error occurs, an error due to data write from an external device or a mistake with operator's procedure can be checked



Record operation log and alarm history

1 Easier to identify error cause from operation log

- Operation logs can be recorded as operation log in an SD memory card or USB memory and can be confirmed in the GOT (HMI) or MELIPC MI3000 on the shop floor
- Data such as operation logs and alarm history can be checked on a computer in time-series
- In addition to operator authentication, recording of specific operator logs can be identified easily




2 Recording of system alarm history

System errors that have occurred are logged in the GOT (HMI) situated on the shop floor. Alarms related to each device with detailed logs showing specific network station number are supported. These features are ideal for large-scale systems.

Simplified analysis

Analysis of recorded data







Replay the video



Waveform data check




GOT (HMI) display

Without the system recorder

- A lot of data when an error occurs is recorded, but linking data is troublesome
- Difficult to trace a program with varying outputs
- Takes time to understand programs created by others
- Troublesome to find reference points for concerns from a video feed

With the system recorder

- The related video feeds, programs, and devices can be linked to check in the same timeline, allowing easier reproduction of the process at an error
- Analysis of programs created by others is easy as relationships of device values and program can be visualized within the flowchart
- As unusual motion is extracted from a video feed and automatically marked, the reference points for concerns can be narrowed down



Log marker function

Faster cause analysis by synchronized video feed, program and waveform monitoring

Register milestone points on the timeline


Milestone points (log marker) can be added to the moment when an error occurs. These points can be saved for later use or for distributing amongst other support personnel enabling multiple people even in the remote location to analyze the problem area of the application.

Categorize registered milestone points

Log markers can be color-coded according to importance and event type with support of commenting, realizing efficient analysis.

Confirming video feed with collected data

After checking the video feed, outputs causing an error and related devices can be tracked as well as programs that change devices. The milestone points (log markers) are synchronized with each software and reproduced at different playback speeds offering a realistic view of the process together with the control data collected.



GX VideoViewer Pro

Difference extraction function





Al technology that extracts differences from the target video by comparing "appearance" and "operation" without deep learning

In addition to the GX VideoViewer functions, differences in a video feed are extracted and marked just with simple setting.

1. Based on Mitsubishi Electric research as of April 28, 2022

Automatically mark differences in the recorded video feed

- Extracts differences in the video feed that differ from normal patterns and adds a mark in the video feed and on the seek bar
- Al analyzes differences of appearance and operation with unique algorithm, enabling easier error analysis
- · Significantly reduce the time to find errors and such occurring at a high-speed which cannot follow with the human eye


Easy 2-step setting


Automatic extraction by unique algorithms can be set up in 2 simple steps:

STEP 1 Set camera images of normal operation. (generation of normal pattern)

STEP 2 Execute difference extraction.

Differences are extracted according to changes in "appearance" and "operation", then marked on the video feed automatically. The log markers can be synchronized with other software.





User benefits

Differences are automatically extracted from the recorded video feed, saving labor time in identifying the cause of abnormalities




Maisart: $\underline{\mathbf{M}}$ itsubishi Electric's $\underline{\mathbf{AI}}$ creates the $\underline{\mathbf{S}}$ tate-of-the- $\underline{\mathbf{ART}}$ in technology Mitsubishi Electric's brand of AI technology aiming to make all devices smarter

Offline monitoring

Synchronized playback of program, waveform data, GOT (HMI) (screens, operation logs, alarm history)

- Playback of data can be done very simply just by loading the recorded data into GX Works3, automatically executing all other necessary tools
- Using the "seek bar" enables to jump back and forth within the timeline synchronizing data between GX Works3 program monitoring (circuit monitor), GX LogViewer (waveform display), and GOT (HMI) (screens, operation logs, alarm history)
- Programming languages such as ladder, ST, FBD, and SFC are supported



GX Works3

Data flow analysis function

1Visualize affected area of device/label


Device and labels together with the affected area can be visualized within the flowchart. The process flow from comments, instruction names, event history, and monitored values can be checked easily identifying the cause of an error.

2Bookmark milestone points

Bookmark milestone points to check speedy.

3 Main program languages supported

Analysis can be done for ladder programs, function block diagram (FBD), SFC (within Zoom) and ST language programs.



GX LogViewer

Simplified analysis of motion control

By loading the motion module/motion CPU module data to GX LogViewer, the axis data shown as a waveform can be easily compared with the programmable controller device data for analysis.

GX Works3


GX LogViewer

GT Designer3

GX VideoViewer

Simplified analysis using panel computer

Multiple data can be reproduced on a panel computer such as the MELIPC MI3000 (embedded Windows® OS). Considering the panel computer is situated on the shop floor, various historical alarms and operation logs can be confirmed efficiently at the point where a problem occurs.



■System recorder related products specifications

System-wide recording Recording function

(device and label collection, image recording)

Recorder module **RD81RC96**

Camera recorder module RD81RC96-CA

Automatic collection of all device changes per programmable controller scan

(with time-stamp) prior to and after an error occurs.

- · Collect all device/label and event history data
- Easily register device trigger and recording time before and after the event
- Network camera image recording (RD81RC96-CA only)



RD81RC96 RD81RC96-CA

Recorder module, camera recorder module specifications

Item		RD81RC96	RD81RC96-CA		
Recording target		Device/label, event history	Device/label, event history, video data		
Number of recording settings		Up	Up to 4		
Recording method		File saving trigger only, recording startup trigger + file saving trigger			
File saving trigger		Device of the control CPU module (rise, fall, timeout), specified time after completion of data accumulation, control CPU module stop error Device of the control CPU module (rise, fall, timeout), specified time after completion of data accum control CPU module stop error, camera e			
Recording startup trigger		Rise/fall (1 per recording setting)			
Sampling method		Each scan, time specification, trigger instruction, safety cycle time			
Number of connectable me	odules	One recorder module per control CPU	Four camera recorder modules per control CPU		
Applicable cameras*1	Camera type	-	ONVIF® Profile S compliant network camera		
	Number of cameras	-	Max. 4 per module*2		
Storage type		SD memory card, file server			
Compatible CPU module		R04/08/16/32/120(EN)CPU, R08/16/32/120SFCPU*3			

- *1. For details of compatible camera, please refer to the technical bulletin (FA-A-0326).
- *2. Up to two units when the recording operation setting is "main" and four units when the recording operation setting is "sub" For details, please refer to the relevant product manual.
- *3. Compatible CPU modules can be checked from product information. Please refer to System recorder device configuration on P.18 and *MELSEC iQ-R CPU User's Manual (Application) (SH-081264ENG).*

System-wide recording Image recording

■ Camera recording package*4

Dedicated function blocks (FB) used in combination with the recorder module.

Camera recording package specifications

	Item	Camera recording package		
Applicable comerce	Camera	AXIS® COMMUNICATIONS (AXIS®) Network camera*5		
Applicable cameras	Applicable carrieras	Amount (max.)	RnCPU:16, RnENCPU:64, RJ71EN71:112*6	
Save destination		File server		
Included item	FB	Time setting, recording direction, virtual input port control		
	Connection guideline	Commercially available network camera and connection and setup guideline for included FBs		
Compatible module	CPU embedded Ethernet port	R00/01/02CPU, R04/08/16/32/120(EN)CPU		
	Ethernet interface module	RJ71EN71		

- *4. For information on obtaining the package, please contact your local Mitsubishi Electric sales office or representative
- * 5. For details of compatible camera, please refer to the technical bulletin (FA-A-0306).
- *6. The maximum number of cameras depends on the amount of available connections not used by other devices. For more information, please refer to "MELSEC iQ-R Ethernet/CC-Link IE User's Manual (Startup) (SH-081256ENG)".

System-wide recording Network camera (Live/PTZ) setting screen

■ Camera adjustment on the operation panel*¹ MI3000 GOT2000 (GT27, GT25)

Sample screens supporting live image streaming and PTZ adjustment of the network camera via the MELSEC iQ-R camera recorder module are available.

*1. For information on obtaining the sample screens, please contact your local Mitsubishi Electric sales office or representative.



System-wide recording Servo system recorder

Motion module

RD78G4 RD78G64 RD78GHV **RD78G8** RD78G16 RD78GHW **RD78G32**

Motion CPU module R16MTCPU R32MTCPU R64MTCPU

Automatic collection of all servo control system drive axes data from the motion module and motion CPU module when an error occurs. Can be used for easy troubleshooting based on command and feedback values.



- Collect servo system recorder data without programming
- Data collection of all drive system axes
- Compare axis data with other logged data on GX LogViewer

Android, Google Play, and Google Play logo are trademarks of Google LLC. App Store is a service mark of Apple Inc.

Windows is a registered trademark of Microsoft Corporation in the United States and other countries.

AXIS is a registered trademark of Axis AB in various jurisdictions.

ONVIF is a trademark of Onvif, Inc.

QR Code is a trademark or a registered trademark of DENSO WAVE INCORPORATED in JAPAN, the United States and/or other countries. All other company names and product names used in this document are trademarks or registered trademarks of their respective companies.

■System recorder related software

GX VideoViewer

Playback of recorded video up to four screens, while freely playing forward one frame, fast-forwarding, and rewinding. Each video can be linked to check in the same timeline. Color-coded log markers can be added to the video timeline, which is useful for analyzing among multiple personnel and inspection. Log markers are synchronized with related engineering software.




GX VideoViewer Pro

In addition to the GX VideoViewer functions, GX VideoViewer Pro automatically extracts differences in a video feed and easily identify an error cause. Differences in the video feed from normal patterns generated during normal operation are extracted based on "appearance (color, shape, position, etc.)" and "operation (movement amount in unit time)," then log markers are automatically added. The error cause can be easily identified in two steps; model generation and difference extraction.



GX LogViewer

GX LogViewer allows observation of device values, which represent quantities that change over time, by zooming in and out of waveforms similar to an oscilloscope. Difference can be checked by superimposing multiple waveforms and observed from repeated patterns and such.



GX Works3

Program steps can be followed and device value changes can be checked by synchronizing the recorded system recorder data with log markers. Data flow analysis visualizes device values and programs affecting the data value change, helping to identify the cause of faults. This can reduce analysis time. Supported programs which synchronize with log markers include not only ladder programs but also function blocks that are easy to follow from the program.



GT Designer3

Screen creation software for GOT (HMI).

GOT (HMI) display/operation log/alarm history can be displayed offline by synchronizing with other applications, making it easier to visualize an error.



^{*} For details on how to obtain the above software, please contact your local Mitsubishi Electric sales office or representative

■System recorder device configuration

Basic configuration

Collecting of all device and label data

- **●**MELSEC iQ-R Series CPU module*1
- **2**Recorder module*2
- **@SD** memory card
- *1. CPU modules with product information (3rd and 4th digits) stated below support collecting of all device and label data.

Model	Product information	Model	Product information	Model	Product information
R04CPU	"19" or later	R04ENCPU	"32" or later	R08SFCPU	"05" or later
R08CPU	"20" or later	R08ENCPU	"30" or later	R16SFCPU	
R16CPU	"20" or later	R16ENCPU	"27" or later	R32SFCPU	
R32CPU	"17" or later	R32ENCPU	"30" or later	R120SFCPU	
R120CPU	"17" or later	R120ENCPU	"22" or later		

For how to check product information, please refer to the "MELSEC iQ-R Module Configuration Manual (SH-081262ENG)". Module firmware update may be required depending on modules.

*2. GX Works3 (Ver.1.065T or later) is necessary for recording setting and module setting GX Works3 (Ver.1.070Y or later) is necessary when using RnSFCPU.



Basic configuration + Camera recording package

Collecting of all device and label data and recording instructions to network camera from software

- **●**MELSEC iQ-R Series CPU module*3
- ②Network camera*4
- **3** Camera recording package (FB and guideline)
- 4 Recorder module*5
- **⑤**SD memory card or file server (NAS or computer)
- 6 PoE switching hub (IEEE802.3at (PoE+) compliant)*6
- *3. CPU modules with product information (3rd and 4th digits) stated below support collecting of all device and label data.

Model	Product information	Model	Product information		
R04CPU	"19" or later	R04ENCPU	"32" or later		
R08CPU	"20" or later	R08ENCPU	"30" or later		
R16CPU	"20" or later	R16ENCPU	"27" or later		
R32CPU	"17" or later	R32ENCPU	"30" or later		
R120CPU	"17" or later	R120FNCPII	"22" or later		

For how to check product information, please refer to the "MELSEC IO-R Module Configuration Manual (SH-081262ENG)". Module firmware update may be required depending on modules.

- To use camera video recording only, below CPU modules can be used.
 - R00/01/02/04/08/16/32/120CPU, R04/08/16/32/120ENCPU (no restriction to product information)
 In addition to the above CPU Ethernet ports, the Ethernet interface module (RJ71EN71) can also
 - In addition to the above CPU Ethernet ports, the Ethernet interface module (RJ71EN71) can als be used
- *4. For details of compatible AXIS® COMMUNICATIONS (AXIS®) Network cameras, please refer to the technical bulletin (FA-A-0306).
- *5. GX Works3 (Ver.1.065T or later) is necessary for recording setting and module setting. GX Works3 (Ver.1.070Y or later) is necessary when using RnSFCPU.
- *6. PoE: Power over Ethernet

Ethernet 6

Basic configuration + Camera recorder module


Collecting of all device and label data, storage of video data from network camera

- MELSEC iQ-R Series CPU module*7*8
- Network camera*9
- **3**Camera recorder module*8
- **4**SD memory card or file server (NAS or computer)
- 6 PoE switching hub (IEEE802.3at (PoE+) compliant)
- *7. CPU modules with product information (3rd and 4th digits) stated below support collecting of all device

and label data.					
Model	Product information	Model	Product information	Model	Product information
R04CPU	"19" or later	R04ENCPU	"32" or later	R08SFCPU	"05" or later
R08CPU	"20" or later	R08ENCPU	"30" or later	R16SFCPU	
R16CPU	"20" or later	R16ENCPU	"27" or later	R32SFCPU	
R32CPU	"17" or later	R32ENCPU	"30" or later	R120SFCPU	
R120CPLI	"17" or later	RIZOFNICELL	"22" or later		

For how to check product information, please refer to the "MELSEC IQ-R Module Configuration Manual (SH-081262ENG)". Module firmware update may be required depending on modules.

- *8. GX Works3 (Ver.1.072A or later) is necessary for recording setting and module and camera setting (not vet supported).
- *9. For details of ONVIF® Profile S compatible network camera and other compatible cameras, please refer to the technical bulletin (FA-A-0326).



Discover the latest information in Factory Automation

Factory Automation Global website

Mitsubishi Electric Factory Automation provides a mix of services to support its customers worldwide.

A consolidated global website is the main portal, offering a selection of support tools and a window to its local Mitsubishi Electric sales and support network.

From here you can find:

- Overview of available factory automation products
- · Library of downloadable literature
- Support tools such as online e-learning courses, terminology dictionary, etc.
- · Global sales and service network portal
- Latest news related to Mitsubishi Electric factory automation



Mitsubishi Electric Factory Automation Global website: www.MitsubishiElectric.com/fa

Mitsubishi Electric FA e-Learning

An extensive library of e-learning courses covering the factory automation product range.

Courses from beginner to advanced levels of difficulty are available anytime anywhere.



Beginner level

Designed for newcomers to Mitsubishi Electric Factory Automation products gaining a background of the fundamentals and an overview of various products related to the course.

Basic to Advanced levels

Various different features are explained along with setup, programming, and network configuration.

Innovative next-generation

e-Manual

A next-generation digital manual that consolidates factory automation products manuals into an easy-to-use package with various useful features.

e-Manual Viewer

Multiple manuals can be cross-searched at once. Multiple users can share the latest manuals and knowhow with document sharing function.



e-Manual Create

Software for converting word files and chm files to e-Manual documents. User's customized machine manuals can be converted to e-Manual documents, allowing consolidated management of user's maintenance information and Mitsubishi Electric product information.

 Country/Region Sales office
 Tel/Fax

 USA
 MITSUBISHI ELECTRIC AUTOMATION, INC.
 Tel : +1-847-478-2100

 500 Corporate Woods Parkway, Vernon Hills, IL 60061, U.S.A.
 Fax : +1-847-478-2253

Mexico MITSUBISHI ELECTRIC AUTOMATION, INC. Mexico Branch Tel : +52-55-3067-7512
Boulevard Miguel de Cervantes Saavedra 301, Torre Norte Piso 5, Ampliacion Granada,

Miguel Hidalgo, Ciudad de Mexico, Mexico, C.P.115200

Brazil MITSUBISHI ELECTRIC DO BRASIL COMERCIO E SERVICOS LTDA. Tel: +55-11-4689-3000
Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brasil Fax: +55-11-4689-3016

Avenida Adelino Cardana, 293, 21 andar, Bethaville, Barueri SP, Brasil Fax: +55-11-4689-3016

MITSUBISHI ELECTRIC EUROPE B.V. German Branch Tel: +49-2102-486-0

Germany MITSUBISHI ELECTRIC EUROPE B.V. German Branch Tel : +49-2102-486-0 Mitsubishi-Electric-Platz 1, 40882 Ratingen, Germany Fax : +49-2102-486-7780

UK MITSUBISHI ELECTRIC EUROPE B.V. UK Branch Travellers Lane, UK-Hatfield, Hertfordshire, AL10 8XB, U.K. Fax: +44-1707-27-8695

IrelandMITSUBISHI ELECTRIC EUROPE B.V. Irish BranchTel : +353-1-4198800Westgate Business Park, Ballymount, Dublin 24, IrelandFax : +353-1-4198890

Italy MITSUBISHI ELECTRIC EUROPE B.V. Italian Branch Tel: +39-039-60531 Centro Direzionale Colleoni - Palazzo Sirio, Viale Colleoni 7, 20864 Agrate Brianza (MB), Italy Fax: +39-039-6053-312

Spain MITSUBISHI ELECTRIC EUROPE, B.V. Spanish Branch
Carretera de Rubi, 76-80-Apdo. 420, E-08190 Sant Cugat del Valles (Barcelona), Spain

Tel : +34-935-65-3131
Fax: +34-935-89-1579

France MITSUBISHI ELECTRIC EUROPE B.V. French Branch Tel: +33-1-55-68-55-68 25, Boulevard des Bouvets, 92741 Nanterre Cedex, France Fax: +33-1-55-68-57-57

Czech Republic MITSUBISHI ELECTRIC EUROPE B.V. Czech Branch, Prague Office Tel: +420-255-719-200 Pekarska 621/7: 155 00 Praha 5. Czech Republic

Poland MITSUBISHI ELECTRIC EUROPE B.V. Polish Branch Tel :+48-12-347-65-00

ul. Krakowska 48, 32-083 Balice, Poland
Sweden MITSUBISHI ELECTRIC EUROPE B.V. (Scandinavia) Tel :+46-8-625-10-00

Hedvig Mollersgata 6, 223 55 Lund, Sweden Fax : +46-46-39-70-18

Russia MITSUBISHI ELECTRIC (RUSSIA) LLC St. Petersburg Branch
Piskarevsky pr. 2. bld 2. lit "Sch". BC "Benua". office 720: 195027 St. Petersburg. Russia Fax: +7-812-633-3499

 Piskarevsky pr. 2, bld 2, lit "Sch", BC "Benua", office 720; 195027 St. Petersburg, Russia
 Fax : +7-812-633-3499

 Turkey
 MITSUBISHI ELECTRIC TURKEY A.S. Umraniye Branch
 Tel : +90-216-969-2500

Serifali Mah. Kale Sok. No:41 34775 Umraniye - İstanbul, Turkey Fax : +90-216-661-4447 UAE MITSUBISHI ELECTRIC EUROPE B.V. Dubai Branch Tel : +971-4-3724716

Dubai Silicon Oasis, P.O.BOX 341241, Dubai, U.A.E. Fax: +971-4-3724721

South Africa ADROIT TECHNOLOGIES Tel: +27-11-658-8100
20 Waterford Office Park, 189 Witkoppen Road, Fourways, South Africa Fax: +27-11-658-8101

China MITSUBISHI ELECTRIC AUTOMATION (CHINA) LTD. Tel : +86-21-2322-3030

Mitsubishi Electric Automation Center, No.1386 Hongqiao Road, Shanghai, China Fax: +86-21-2322-3000
Taiwan SETSUYO ENTERPRISE CO., LTD. Tel: +886-2-2299-2499

 Taiwan
 SETSUYO ENTERPRISE CO., LTD.
 Tel : +886-2-2299-2499

 6F, No.105, Wugong 3rd Road, Wugu District, New Taipei City 24889, Taiwan
 Fax : +886-2-2299-2509

Korea MITSUBISHI ELECTRIC AUTOMATION KOREA CO., LTD. Tel : +82-2-3660-9569 7F to 9F, Gangseo Hangang Xi-tower A, 401, Yangcheon-ro, Gangseo-Gu, Seoul 07528, Korea Fax : +82-2-3664-8372

Singapore MITSUBISHI ELECTRIC ASIA PTE. LTD. Tel :+65-6473-2308

307 Alexandra Road, Mitsubishi Electric Building, Singapore 159943

Thailand MITSUBISHI ELECTRIC FACTORY AUTOMATION (THAILAND) CO., LTD. Tel: +66-2682-6522-31 12th Floor, SV.City Building, Office Tower 1, No. 896/19 and 20 Rama 3 Road, Fax: +66-2682-6020

Kwaeng Bangpongpang, Khet Yannawa, Bangkok 10120, Thailand

Vietnam MITSUBISHI ELECTRIC VIETNAM COMPANY LIMITED
Unit 01-04, 10th Floor, Vincom Center, 72 Le Thanh Ton Street, District 1, Ho Chi Minh City, Vietnam
Tel: +84-28-3910-5945
Fax: +84-28-3910-5947

Indonesia PT. MITSUBISHI ELECTRIC INDONESIA Tel : +62-21-31926461

Gedung Jaya 8th Floor, JL. MH. Thamrin No.12, Jakarta Pusat 10340, Indonesia Fax: +62-21-31923942

India MITSUBISHI ELECTRIC INDIA PVT. LTD. Pune Branch Tel : +91-20-2710-2000 Emerald House, EL-3, J Block, M.I.D.C., Bhosari, Pune-411026, Maharashtra, India Fax: +91-20-2710-2100

Australia MITSUBISHI ELECTRIC AUSTRALIA PTY. LTD. Tel : +61-2-9684-7777

348 Victoria Road, P.O. Box 11, Rydalmere, N.S.W 2116, Australia Fax: +61-2-9684-7245



Mitsubishi Electric's e-F@ctory concept utilizes both FA and IT technologies, to reduce the total cost of development, production and maintenance, with the aim of achieving manufacturing that is a "step ahead of the times". It is supported by the e-F@ctory Alliance Partners covering software, devices, and system integration, creating the optimal e-F@ctory architecture to meet the end users needs and investment plans.



MITSUBISHI ELECTRIC CORPORATION

HEAD OFFICE: TOKYO BLDG., 2-7-3, MARUNOUCHI, CHIYODA-KU, TOKYO 100-8310, JAPAN

www.MitsubishiElectric.com